#### Hydrogen Oxygen Separation With Zero Ozone A true Hydrogen Rich Water Cup



Cup body material : American Eastman tritan material	Material of cup lid: Aluminum alloy
Maximum power: ≤ 5W	Base electrode: Platinum Titanium
Potential range: -650 ~ 0mv	Whole cup size: 220mm
Hydrogen concentration:2000-9000PPb	Cup diameter: 65mm
Charge Port: Type-C	Cup capacity: 400 ml


New generation hydrogen production technology

#### Hydrogen production by dual-mode cavity

Hydrogen molecular
min content up to 2000 PPb

18<sub>mi</sub>

Hydrogen molecular min content up to 6000 PPb



# 18 MIN GENERATION

#### Multiple functions of one machine



DIVERSE



- Direct drink
- transfer mineral water
- hydrogen absorption machine










### FREE RADICAL CLEANING START TRANSFORMING NOW

Medical research has found that hydrogen can selectively neutralize toxic free radicals in the body and generate non-toxic, harmless water, thus protecting body cells from toxic free radical damage.



Hydrogen enters the cell, synthesizes water from free radicals, and excretes it from the body.

## FREE RADICAL



Double Membrane Cavity



Tritan material does not contain bisphenol A



18-minute hydrogen absorption mode



Hot and cold water universal



**Effcient Endurance** 



1 Machine for3 Purpose



